




## OnTrack Rotary Bottle Orienter



### Standard Features

Fast, versatile, easy to operate and maintain, Ontrack orienters are custom-configured in various frame sizes and head configurations and can handle glass or plastic containers of almost any size or shape. Standard features include automatic speed controls, fingertip settings, digital speed read-out, and power height adjustment.

# OnTrack Rotary Bottle Orienter

## Fast

- Testing speeds up to 600 containers per minute
- Exclusive 'QC' Quick Change bottle handling parts

## Versatile

- Choose from various frame sizes, and head configurations
- Glass or plastic containers of almost any size or shape
- 90°, 180°, 270° bottle orientation capabilities
- Appropriate sensing system to suit container
- Programmable PLC controls
- Variable frequency drive

## Easy to Operate

- Automatic speed controls with fingertip settings
- Digital speed read-out in containers per minute
- Power height adjustment

## Easy to Maintain

- Stainless steel and aluminum construction
- High quality, with years of proven reliability
- Low operating cost

## Additional Features

- Dual feed screw system
- Synchronous drive arrangement
- Multiple configurations available to suit specific applications requirements

## Options

- Dual feed screw system
- Synchronous drive arrangement
- Multiple configurations available to suit specific applications requirements

Angelus | Carr Centritech | Consolidated | Continental/Closetech | Hema  
Mateer Burt | Multi-Tech Systems | OnTrack | Zepf Change Parts

### Pneumatic Scale Angelus

4485 Allen Road  
Stow, OH 44224 USA

t. +1 (330) 923-0491  
[psangelus.com](http://psangelus.com)